

## Closed aluminum transport carts



These modular trolleys in anodised aluminum are produced according to ISO and DIN measurements. The nylon guides, on which stainless steel as well as PC, ABS or polypropylene baskets or modules can rest, guarantee a smooth and noiseless transport. The distance between the guides is 114 mm as standard.

Equipped with an extra bumper at the top of the trolley and using a lock, the aluminum transport trolley is a safe and ergonomic means of internal transport of sterile and non-sterile goods.

This transport cart is best cleaned manually. The use of aluminum trolleys in washing tunnels is not recommended, as the material will tarnish. For a washing tunnel resistant trolley, we recommend our range of stainless steel trolleys.

Our closed ISO aluminum transport carts allow you to safely and hygienically transport sterile and non-sterile goods or medication from your storage, sterilization unit or pharmacy to the relevant delivery points.



### »» Tow bar mechanism

The base of the aluminum carts can be fitted with a tow bar to allow you to couple several carts together so that they can be operated as one single unit.

For enhanced manoeuvrability, both sides of the cart have been fitted with a push bar.



### »» Removable ladders

If necessary, the ladders with the guides can be dismantled to allow for easy cleaning of the trolley.

The standard distance between the runners is 114 mm.



### »» Castors

The transport carts are delivered with 200 mm diameter castors. These make for low rolling resistance and ensure that the transport cart is easy to manoeuvre.

Our 1-column, D-type transport carts have been fitted with smaller castors of 125 mm in diameter.

## » Closed aluminium transport carts - Overview

Basic version	19032 00001	19032 00002	19032 00003	19032 00004	19032 00005	19032 00006	19032 00007	19032 00008	19032 00009
All models inclusive of cylinder lock with key set, A4 document holder and brake on the swivel wheel									
Number of columns	ISO 1	ISO 1	ISO 2	ISO 2	ISO 3	ISO 3	DIN 2	ISO 3	ISO 2
Number of runners	12 pair	9 pair	2 x 12 pair	2 x 9 pair	3 x 12 pair	3 x 9 pair	2 x 9 pair	3 x 6 pair	2 x 6 pair
Usable positions (B = Baskets, S = Shelves)	12B 11S	9B 8S	2 x 12B 2 x 11S	2 x 9B 2 x 9S	3 x 12B 3 x 11S	3 x 9B 3 x 9S	2 x 9S	3 x 6B 3 x 6S	2 x 6B 2 x 6S
Document holder	✓	✓	✓	✓	✓	✓	✓	✓	✓
Drawbar	-	-	-	-	-	-	-	-	-
Model	High	Low	High	Low	High	Low	Low	Low	Low
Height in mm	1665	1500	1750	1500	1750	1500	1500	1500	1500
Diameter wheels in mm	125	125	200	200	200	200	200	200	200
Load capacity	25 kg per pair of runners - 150 kg per column - 300 kg per cart								
Filling									
ISO Perfo-Safe® wire shelves	✓	✓	✓	✓	✓	✓	-	✓	✓
ISO Perfo-Safe® wire baskets	✓	✓	✓	✓	✓	✓	-	✓	✓
ISO Perfo-Safe® wire shelf with raised edge (Delphine)	✓	✓	✓	✓	✓	✓	-	✓	✓
DIN Perfo-Safe® wire shelves	-	-	-	-	-	-	✓	-	-

Full option version	19032 00010	19032 00011	19032 00012	19032 00013	19032 00014	19032 00015	19032 00016	19032 00017	19032 00018
All models inclusive of cylinder lock with key set, A4 document holder and brake on the swivel wheel, rubber bumper at the top, tow bar and coupling hook									
Number of columns	ISO 1	ISO 1	ISO 2	ISO 2	ISO 3	ISO 3	DIN 2	ISO 3	ISO 2
Number of runners	12 pair	9 pair	2 x 12 pair	2 x 9 pair	3 x 12 pair	3 x 9 pair	2 x 9 pair	3 x 6 pair	2 x 6 pair
Usable positions (B = Baskets, S = Shelves)	12B 11S	9B 8S	2 x 12B 2 x 11S	2 x 9B 2 x 9S	3 x 12B 3 x 11S	3 x 9B 3 x 9S	2 x 9S	3 x 6B 3 x 6S	2 x 6B 2 x 6S
Document holder	✓	✓	✓	✓	✓	✓	✓	✓	✓
Drawbar	✓	✓	✓	✓	✓	✓	✓	✓	✓
Model	High	Low	High	Low	High	Low	Low	Low	Low
Height in mm	1665	1500	1750	1500	1750	1500	1500	1500	1500
Diameter wheels in mm	125	125	200	200	200	200	200	200	200
Load capacity	25 kg per pair of runners - 150 kg per column - 300 kg per cart								
Filling									
ISO Perfo-Safe® wire shelves	✓	✓	✓	✓	✓	✓	-	✓	✓
ISO Perfo-Safe® wire baskets	✓	✓	✓	✓	✓	✓	-	✓	✓
ISO Perfo-Safe® wire shelf with raised edge (Delphine)	✓	✓	✓	✓	✓	✓	-	✓	✓
DIN Perfo-Safe® wire shelves	-	-	-	-	-	-	✓	-	-