

Linen and waste treatment

# Linen and waste treatment

Linen and waste collectors	
Linen and waste collectors - Accessories5	
Shutty Waste Collectors and Coupled Shutty7	
Shelved trolleys: Open - Closed - Linkable11	
Waste transport trolleys	

Belint Part Registered Trademarks or Patent Pending Trademarks of BELINTRA NV or BELINTRA, Inc
BELINTRA NV - CAT/0002/DE - 02/2023 - No reproduction allowed without prior written consent
Images for illustrative purposes, not binding.



### Linen and waste collectors



The stainless steel collectors allow for easy and hygienic collection of dirty linen and waste. By equipping the linen collector with a bottom plate, it can be used as a waste collector. The mobile collectors are available in different sizes and types for different purposes.

All models are made of stainless steel and all welds are welded all around for optimum strength and hygiene. When you choose a linen or waste collector with lids, you can choose the colours of the lids and specify these with the order.

The collectors are equipped with rubber Care rings which are designed for bags of approximately  $600 \times 1000 \text{ mm}$  (measured flat).

Thanks to the rubber Care ring, the bags are securely and hygienically attached.



#### Rubber Care ring

The rubber Care ring ensures that the linen or waste bag remains securely and hygienically in place. It is designed in such a way that the outside of the bag cannot get dirty and the ring is easy to clean.



#### Pedal operation

The pedal mechanism consists of nicely rounded parts. The system is ergonomic, robust and maintenance-free.



#### Soft-closing systeem

The hinge has no weak points and is equipped with an integrated soft-closing system. The soft-closing system ensures that the lid closes quietly and gently.

### >> Linen and waste collectors - Basic models without accessories



1-ring without a	occessories	
Article Number	Description	External dimensions
20003 00005	1-ring without accessories	400 x 500 x 910 mm



2-rings without accessories		
Article Number	Description	External dimensions
20003 00006	2-rings without accessories	750 x 500 x 910 mm



3-rings without accessories		
Article Number	Description	External dimensions
20003 00007	3-rings without accessories	1100 x 500 x 910 mm



4-rings without accessories		
Article Number	Description	External dimensions
20003 00008	4-rings without accessories	1450 x 500 x 910 mm



4-rings without	accessories -	-	square
-----------------	---------------	---	--------

Article Number	Description	External dimensions
20003 00009	4-rings without accessories - square	1100 x 750 x 910 mm



# Linen and waste collectors - Accessories



)) Pedal	
Article Number	Description
20003 00210	One to be provided per ring



>> ABS lids	
Article Number	Description
20003 00017	Blue
20003 00023	Green
20003 00024	Yellow
20003 00025	Brown
20003 00026	Red
20003 00027	White

### >> Colour examples of the lids



When you choose linen or waste collectors with lids, you can choose the colours of the lids and you must specify them with your order.

### )) Linen and waste collectors - Accessories



Push handle	
Article Number	Description
20003 00016	One per collector



Bottom plate to configure the waste collectors		
Article Number	Description	
20003 00258	1-ring	
20003 00001	2-rings	
20003 00002	3-rings	
20003 00003	4-rings	
20003 00004	4-rings – square	



Nubber Care ring		
Article Number	Description	
20003 00221	One to be provided per ring	



Disinfection Disp	Denser
Article Number	Description
20003 00268	Dispenser 500 – 1000ml



# Shutty Waste Collectors and Coupled Shutty



The Shutty is suitable for the airtight collection of waste. The waste collector opens and closes thanks to the pedal control, partially covered with plastic.

When opening the Shutty, the car locks automatically and can no longer roll away.

The airtight sealing ring has a clamp for waste bags of 575 x 1000 mm (measured flat) with a capacity of 70 litres.

The coupled combination collectors are designed for collecting dirty linen and waste. They combine the collector and the Shutty.

The simple and sturdy mechanism of the waste collector ensures that the waste bag always remains airtight closed.



### Airtight sealing ring

The rubber sealing ring ensures that the waste bag always remains airtight. Thanks to the pedal mechanism, the ring can be opened easily and hygienically.



### Extra clamp

The Shutty is equipped with an extra plastic clamp, so that waste bags are kept in place during transfers.



### Stainless steel design

The frame is made of stainless steel so that the Shutty can be completely cleaned.

## >> Shutty waste collectors



Shutty waste collector		
Article Number	Content	External dimensions
20004 00012	70	500 x 600 x 990 mm
20004 00011	40	500 x 600 x 830 mm



Shutty for wall	mounting	
Article Number	Content	External dimensions
20004 00005	70	390 x 600 x 790 mm



Stationary Shutty		
Article Number	Content	External dimensions
20004 00015	70	470 x 600 x 990 mm
20004 00016	40	470 x 600 x 830 mm

## >> Connected Shutty waste collectors



### )) Combination collector with 1 ring and Shutty

Article Number	Description
20003 00005	1 ring without accessories
20004 00012	Shutty waste collector
20004 00009	Coupling system

Combination collector with 2 rings and Shutty	
Article Number	Description
20003 00006	2 rings without accessories
20004 00012	Shutty waste collector
20004 00009	Coupling system

Combination collector with 3 rings and Shutty		
Article Number	Description	
20003 00007	3 rings without accessories	
20004 00012	Shutty waste collector	
20004 00009	Coupling system	





# Shelved trolleys: Open - Closed - Linkable







The 1-part shelved trolleys are used for the distribution of clean linen. The 2-part can be used for the same and simultaneous collection of dirty linen.

The rugged frame is made of AISI 304 stainless steel (1.4301) completely TIG welded at all joints to avoid water infiltration and dirt collection, ensuring perfect hygiene. Bottom, shelves and dividing wall are made of 18 mm thick wood panels, covered with melamine sheet and with ABS profiles along the edge. The two tubes running above the worktop build a comfortable push handle.

We can also offer different types of shelf trolleys in our range. Please contact your account manager or our customer service to discuss the wider range.

## >> Shelved trolleys: Open - Closed - Linkable



#### Closed 2-part (clean/dirty) shelved trolley

Article Number	Description	External dimensions
20003 00369	2 inner shelves + worktop + 2 rings 350x255	1120 x 1410 x 500 mm



Closed 2-part (clean/dirty) shelved trolley		
Article Number	Description	External dimensions
20003 00370	2 shelves + worktop + 2 rings 350x255	1120 x 1100 x 660 mm



Closed 1-part shelved trolley		
Article Number	Description	External dimensions
20003 00371	2 inner shelves + worktop + drawer	1320 x 680 x 660 mm



## Waste transport trolleys



These aluminium trolleys are used to collect dirty linen and waste.

The inside of the car can be easily cleaned with water, as the optional drain valve ensures that the water can drain easily.

The waste transport cart is equipped with a lid and a front panel that partially folds down to facilitate loading and unloading.



#### Front panel

The waste transport cart is equipped with a lid and a front panel that partially folds down to facilitate loading and unloading.



### Closure

The closure on the hinge blocks the lid when open so that it cannot fall shut.



#### Drain tap

The inside of the car can be easily cleaned with water, as the optional drain valve ensures that the water can drain easily.

# >> Waste transport trolleys



### >>> Waste transport trolley

woste dousport douey		
Article Number	Volume	External dimensions
20006 00008	720 I	1090 x 690 x 1515 mm
20006 00027	1100 l	1410 x 730 x 1515 mm



>>> Waste transport trolley with tap		
Article Number	Volume	External dimensions
Upon request	7201	1090 x 690 x 1515 mm
Upon request	1100	1410 x 730 x 1515 mm

4.15

